

Teknisk specifikation

SIS-ISO/TS 16610-32:2009

Publicerad/Published: 2009-05-05

Utgåva/Edition: 1

Språk/Language: engelska/English

ICS: 17.040.20

**Geometriska produktspecifikationer (GPS) – Filtrering –
Del 32: Robusta profilfilter: Splinesfilter
(ISO/TS 16610-32:2009, IDT)**

**Geometrical product specification (GPS) – Filtration –
Part 32: Robust profile filters: Spline filters
(ISO/TS 16610-32:2009, IDT)**

This preview is downloaded from www.sis.se. Buy the entire standard via <https://www.sis.se/std-69167>

Hitta rätt produkt och ett leveranssätt som passar dig

Standarder

Genom att följa gällande standard både effektiviserar och säkrar du ditt arbete. Många standarder ingår dessutom ofta i paket.

Tjänster

Abonnemang är tjänsten där vi uppdaterar dig med aktuella standarder när förändringar sker på dem du valt att abonnera på. På så sätt är du säker på att du alltid arbetar efter rätt utgåva.

e-nav är vår online-tjänst som ger dig och dina kollegor tillgång till standarder ni valt att abonnera på dygnet runt. Med e-nav kan samma standard användas av flera personer samtidigt.

Leveranssätt

Du väljer hur du vill ha dina standarder levererade. Vi kan erbjuda dig dem på papper och som pdf.

Andra produkter

Vi har böcker som underlättar arbetet att följa en standard. Med våra böcker får du ökad förståelse för hur standarder ska följas och vilka fördelar den ger dig i ditt arbete. Vi tar fram många egna publikationer och fungerar även som återförsäljare. Det gör att du hos oss kan hitta över 500 unika titlar. Vi har även tekniska rapporter, specifikationer och "workshop agreement".

Matriser är en översikt på standarder och handböcker som bör läsas tillsammans. De finns på sis.se och ger dig en bra bild över hur olika produkter hör ihop.

Standardiseringsprojekt

Du kan påverka innehållet i framtida standarder genom att delta i någon av SIS ca 400 Tekniska Kommittéer.

Find the right product and the type of delivery that suits you

Standards

By complying with current standards, you can make your work more efficient and ensure reliability. Also, several of the standards are often supplied in packages.

Services

Subscription is the service that keeps you up to date with current standards when changes occur in the ones you have chosen to subscribe to. This ensures that you are always working with the right edition.

e-nav is our online service that gives you and your colleagues access to the standards you subscribe to 24 hours a day. With e-nav, the same standards can be used by several people at once.

Type of delivery

You choose how you want your standards delivered. We can supply them both on paper and as PDF files.

Other products

We have books that facilitate standards compliance. They make it easier to understand how compliance works and how this benefits you in your operation. We produce many publications of our own, and also act as retailers. This means that we have more than 500 unique titles for you to choose from. We also have technical reports, specifications and workshop agreements. Matrices, listed at sis.se, provide an overview of which publications belong together.

Standardisation project

You can influence the content of future standards by taking part in one or other of SIS's 400 or so Technical Committees.

Denna tekniska specifikation är inte en svensk standard. Detta dokument innehåller den engelska språkversionen av ISO/TS 16610-32:2009.

This Technical Specification is not a Swedish Standard. This document contains the English version of ISO/TS 16610-32:2009.

! © Copyright/Upphovsrätten till denna produkt tillhör SIS, Swedish Standards Institute, Stockholm, Sverige. Användningen av denna produkt regleras av slutanvändarlicensen som återfinns i denna produkt, se standardens sista sidor.

■ © Copyright SIS, Swedish Standards Institute, Stockholm, Sweden. All rights reserved. The use of this product is governed by the end-user licence for this product. You will find the licence in the end of this document.

Upplysningar om sakinnehållet i standarden lämnas av SIS, Swedish Standards Institute, telefon 08-555 520 00. Standarder kan beställas hos SIS Förlag AB som även lämnar allmänna upplysningar om svensk och utländsk standard.

Information about the content of the standard is available from the Swedish Standards Institute (SIS), tel +46 8 555 520 00. Standards may be ordered from SIS Förlag AB, who can also provide general information about Swedish and foreign standards.

SIS Förlag AB, SE 118 80 Stockholm, Sweden. Tel: +46 8 555 523 10. Fax: +46 8 555 523 11.
E-mail: sis.sales@sis.se Internet: www.sis.se

Contents		Page
Foreword.....		iv
Introduction		vi
1 Scope		1
2 Normative references		1
3 Terms and definitions.....		1
4 Robust spline filters		2
4.1 Weighting function		2
4.2 Filter equations		2
4.2.1 General.....		2
4.2.2 Filter equation of the robust spline filter for open profiles		2
4.2.3 Filter equation of the robust spline filter for closed profiles		3
4.3 Transmission characteristic		3
5 Recommendations.....		4
5.1 Nesting index (cut-off value λ_c).....		4
5.2 Tension parameter (β)		4
5.3 Implementation		4
5.4 Filter designation		4
Annex A (informative) Examples		5
Annex B (informative) Relationship to the filtration matrix model.....		8
Annex C (informative) Relation to the GPS matrix model.....		9
Bibliography		10

Foreword

ISO (the International Organization for Standardization) is a worldwide federation of national standards bodies (ISO member bodies). The work of preparing International Standards is normally carried out through ISO technical committees. Each member body interested in a subject for which a technical committee has been established has the right to be represented on that committee. International organizations, governmental and non-governmental, in liaison with ISO, also take part in the work. ISO collaborates closely with the International Electrotechnical Commission (IEC) on all matters of electrotechnical standardization.

International Standards are drafted in accordance with the rules given in the ISO/IEC Directives, Part 2.

The main task of technical committees is to prepare International Standards. Draft International Standards adopted by the technical committees are circulated to the member bodies for voting. Publication as an International Standard requires approval by at least 75 % of the member bodies casting a vote.

In other circumstances, particularly when there is an urgent market requirement for such documents, a technical committee may decide to publish other types of normative document:

- an ISO Publicly Available Specification (ISO/PAS) represents an agreement between technical experts in an ISO working group and is accepted for publication if it is approved by more than 50 % of the members of the parent committee casting a vote;
- an ISO Technical Specification (ISO/TS) represents an agreement between the members of a technical committee and is accepted for publication if it is approved by 2/3 of the members of the committee casting a vote.

An ISO/PAS or ISO/TS is reviewed after three years in order to decide whether it will be confirmed for a further three years, revised to become an International Standard, or withdrawn. If the ISO/PAS or ISO/TS is confirmed, it is reviewed again after a further three years, at which time it must either be transformed into an International Standard or be withdrawn.

Attention is drawn to the possibility that some of the elements of this document may be the subject of patent rights. ISO shall not be held responsible for identifying any or all such patent rights.

ISO/TS 16610-32 was prepared by Technical Committee ISO/TC 213, *Dimensional and geometrical product specifications and verification*.

ISO 16610 consists of the following parts, under the general title *Geometrical product specifications (GPS) — Filtration*:

- *Part 1: Overview and basic concepts* [Technical Specification]
- *Part 20: Linear profile filters: Basic concepts* [Technical Specification]
- *Part 21: Linear profile filters: Gaussian filters*
- *Part 22: Linear profile filters: Spline filters* [Technical Specification]
- *Part 29: Linear profile filters: Spline wavelets* [Technical Specification]
- *Part 30: Robust profile filters: Basic concepts* [Technical Specification]
- *Part 32: Robust profile filters: Spline filters* [Technical Specification]

- *Part 40: Morphological profile filters: Basic concepts* [Technical Specification]
- *Part 41: Morphological profile filters: Disk and horizontal line-segment filters* [Technical Specification]
- *Part 49: Morphological profile filters: Scale space techniques* [Technical Specification]

The following parts are under preparation:

- *Part 28: Profile filters: End effects* [Technical Specification]
- *Part 31: Robust profile filters: Gaussian regression filters* [Technical Specification]

The following parts are planned:

- *Part 26: Linear profile filters: Filtration on nominally orthogonal grid planar data sets*
- *Part 27: Linear profile filters: Filtration on nominally orthogonal grid cylindrical data sets*
- *Part 42: Morphological profile filters: Motif filters*
- *Part 60: Linear areal filters: Basic concepts*
- *Part 61: Linear areal filters: Gaussian filters*
- *Part 62: Linear areal filters: Spline filters*
- *Part 69: Linear areal filters: Spline wavelets*
- *Part 70: Robust areal filters: Basic concepts*
- *Part 71: Robust areal filters: Gaussian regression filters*
- *Part 72: Robust areal filters: Spline filters*
- *Part 80: Morphological areal filters: Basic concepts*
- *Part 81: Morphological areal filters: Sphere and horizontal planar segment filters*
- *Part 82: Morphological areal filters: Motif filters*
- *Part 89: Morphological areal filters: Scale space techniques*

Introduction

This part of ISO 16610 is a geometrical product specification (GPS) standard and is to be regarded as a global GPS standard (see ISO/TR 14638). It influences the chain links 3 and 5 of all chains of standards.

For more detailed information of the relation of this part of ISO 16610 to the GPS matrix model, see Annex C.

This part of ISO 16610 develops the terminology and concepts of robust spline filters. The robust spline filter has the advantage over a conventional phase correct filter that the edges of the measured profile are still usable. This is important especially in the case of form filtering. Moreover, the robust spline filter is tolerant against outliers.

Geometrical product specifications (GPS) — Filtration —

Part 32: Robust profile filters: Spline filters

1 Scope

This part of ISO 16610 specifies the characteristics of robust spline filters for surface profiles.

It specifies in particular how to separate the long and short wave content of a surface profile.

2 Normative references

The following referenced documents are indispensable for the application of this document. For dated references, only the edition cited applies. For undated references, the latest edition of the referenced document (including any amendments) applies.

ISO 4287:1997, *Geometrical Product Specifications (GPS) — Surface texture: Profile method — Terms, definitions and surface texture parameters*

ISO/TS 16610-1:2006, *Geometrical product specifications (GPS) — Filtration — Part 1: Overview and basic concepts*

ISO/TS 16610-22:2006, *Geometrical product specifications (GPS) — Filtration — Part 22: Linear profile filters: Spline filters*

ISO/TS 16610-30:2009, *Geometrical product specifications (GPS) — Filtration — Part 30: Robust profile filters: Basic concepts*

ISO/IEC Guide 99:2007, *International vocabulary of metrology — Basic and general concepts and associated terms (VIM)*

3 Terms and definitions

For the purposes of this document, the terms and definitions given in ISO/IEC Guide 99, ISO 4287, ISO/TS 16610-1, ISO/TS 16610-22, ISO/TS 16610-30 and the following apply.

3.1

robust spline filter

robust filter based on splines

NOTE 1 The result of the low-pass filtering (the mean line) is a spline.

NOTE 2 The degree of the spline is equal to the degree of the polynomial of highest degree used, e.g. a cubic spline is made of cubic polynomials.

NOTE 3 Robust spline filters are non-linear filters.

4 Robust spline filters

4.1 Weighting function

The weighting function of a robust spline filter does not exist because this filter is non-linear.

4.2 Filter equations

4.2.1 General

Filter equations for robust spline filters may be constructed for any degree, but only those based on cubic splines are given here.

4.2.2 Filter equation of the robust spline filter for open profiles

The filter equation is given by

$$\left[\beta \alpha^2 P + (1 - \beta) \alpha^4 Q \right] w = \frac{\text{sgn}(z - w)}{\sum |(z - w)|} \quad (1)$$

with the matrix

$$P = \begin{pmatrix} 1 & -1 & & & & & \\ -1 & 2 & -1 & & & & \\ & -1 & 2 & -1 & & & \\ & & \ddots & \ddots & \ddots & & \\ & & & -1 & 2 & -1 & \\ & & & & -1 & 2 & -1 \\ & & & & & -1 & 1 \end{pmatrix} \quad Q = \begin{pmatrix} 1 & -2 & 1 & & & & \\ -2 & 5 & -4 & 1 & & & \\ 1 & -4 & 6 & -4 & 1 & & \\ & \ddots & \ddots & \ddots & \ddots & \ddots & \\ & & & 1 & -4 & 6 & -4 & 1 \\ & & & & 1 & -4 & 5 & -2 \\ & & & & & 1 & -2 & 1 \end{pmatrix} \quad (2)$$

with n rows and n columns and the parameters

$$\alpha = \frac{1}{2 \sin \frac{\pi \Delta x}{\lambda_c}} \quad \text{and} \quad 0 \leq \beta \leq 1 \quad (3)$$

where

- n is the number of measured values of the profile;
- z is the vector of dimension n of the profile values before filtering;
- w is the vector of dimension n of this profile's values in the reference line;
- λ_c is the limiting wavelength of the profile filter;

Δx is the sampling interval

$$\text{sgn}(t) = \begin{cases} +1 & \text{if } t \geq 0 \\ -1 & \text{if } t < 0 \end{cases}$$

NOTE 1 The vector w gives the profile values of the long wave component (reference line). The short wave component, r , may be obtained by the difference vector $r = z - w$, i.e. by subtracting the mean line values obtained by the filtering process from the measured profile values.

NOTE 2 The β value of 0,625 242... gets the spline filter as close as possible to the Gaussian filter.

4.2.3 Filter equation of the robust spline filter for closed profiles

The filter equation is given by

$$\left[\beta \alpha^2 \tilde{P} + (1 - \beta) \alpha^4 \tilde{Q} \right] \tilde{w} = \frac{\text{sgn}(\tilde{z} - \tilde{w})}{\sum |(\tilde{z} - \tilde{w})|} \quad (4)$$

with the matrix

$$\tilde{P} = \begin{pmatrix} 2 & -1 & & & & & -1 \\ -1 & 2 & -1 & & & & \\ & -1 & 2 & -1 & & & \\ & & \ddots & \ddots & \ddots & & \\ & & & -1 & 2 & -1 & \\ & & & & -1 & 2 & -1 \\ -1 & & & & & -1 & 2 \end{pmatrix} \quad \tilde{Q} = \begin{pmatrix} 6 & -4 & 1 & & & & 1 & -4 \\ -4 & 6 & -4 & 1 & & & & 1 \\ 1 & -4 & 6 & -4 & 1 & & & \\ & \ddots & \ddots & \ddots & \ddots & \ddots & & \\ & & & 1 & -4 & 6 & -4 & 1 \\ 1 & & & & 1 & -4 & 6 & -4 \\ -4 & 1 & & & & 1 & -4 & 6 \end{pmatrix} \quad (5)$$

with n rows and n columns and the parameters

$$\alpha = \frac{1}{2 \sin \frac{\pi \Delta x}{\lambda_c}} \quad \text{and} \quad 0 \leq \beta \leq 1 \quad (6)$$

where

n is the number of measured values of the profile;

\tilde{z} is the vector of dimension n of the profile values before filtering;

\tilde{w} is the vector of dimension n of this profile's values in the mean line;

λ_c is the limiting wavelength of the profile filter;

Δx is the sampling interval.

NOTE The vector \tilde{z} gives the profile values of the long wave component (mean line). The short wave component, \tilde{r} , may be obtained by the difference vector $\tilde{r} = \tilde{z} - \tilde{w}$, i.e. by subtracting the mean line values obtained by the filtering process from the measured profile values.

4.3 Transmission characteristic

The transmission characteristic of a robust spline filter does not exist because this filter is non-linear, i.e. no weighting function exists.